



Machining Guides for DIAbide™ Cutting Tools

Green Ceramic

Machining green ceramic with diamond tools

CVD diamond tools are a perfect match for machining unfired aluminum oxide, tungsten carbide, silicon carbide, and other green ceramics. The abrasive nature of these materials severely limits the life of carbide tools, and PCD diamond tools are not available in the small, multi-flute configurations required for machining fine detail.

Tools with diamond on the surface wear longer and have a lower coefficient of friction. These characteristics provide substantial benefit to the machining operation.

Because diamond tools last much longer—10 to 50 times the life of carbide—they:

- Improve the dimensional accuracy and consistency of the machined parts
- Greatly reduce the number of tool changes, increasing productivity
- Increase machine utilization
- Allow much longer periods of unattended machining, e.g., overnight
- Quickly pay for themselves

The low friction of CVD diamond tools permits using speeds 2 to 3 times higher than carbide—again contributing to productivity—with no degradation of surface quality. The consistently sharp edge and low friction allows delicate, thin-wall sections to be machined quickly and precisely at high rpm settings with reduced feed rates.


Examples of green ceramic machining applications

A major manufacturer of ceramic components for the semiconductor industry had a problem making a gas diffusion furnace component with 24 slots cut at an angle through the full depth of the part. Machining this part with uncoated carbide 3/8" endmills typically required 10 tools to complete one part.

While the entire milling operation—about 1½ hours—ran under CNC control, the machinist had to watch continuously for the onset of chipping as a tool wore out, since chipping or cracking would invalidate the part—an expensive throwaway, especially if the part was almost fully machined.



Switching to *sp*³ DIAbide endmills, one tool easily completes 5 parts—a 50 times gain in tool life. The extended tool life allows these parts to be machined unattended. In this application, speeds are increased 10–20%, and feeds about double.



Drilling with a 3/64" drill. When finished, this part will have 87 holes. One diamond drill will complete 10 parts.

Drilling is another instance where long, reliable wear life of tool cutting edges is important. Drill wear causes breakout and edge chipping, making the product unacceptable. *sp*³ DIAbide drills are now used, in diameters as small as 0.018".

A manufacturer of precision ceramic parts for semiconductor, electronics, and medical device production switched to DIAbide tools to reduce tool change downtime.

Inserts are used for turning alumina billets, then endmills and drills are employed for machining fine detail to tolerances on the order of 0.005". For a typical job using a 0.200" diameter endmill, two parts can be machined with carbide—vs. 800 parts with the diamond tool. Savings in downtime for tool resharping or replacement in this and other operations has allowed parts to be made that would have been unprofitable with carbide tools. In this application the *sp*³ tools are run at speeds and feeds about 15% higher than carbide.



In turning soft alumina, diamond inserts last almost indefinitely.



A central vacuum system captures the dust produced by endmilling and other machining operations.



Typical finished ceramic parts.

For assistance call: 800-773-9940

Visit our website: www.sp3inc.com

General tool conditions for machining green ceramic

The green ceramic cutting process

In any machining process, a wear-resistant cutting edge separates material from the workpiece because of the velocity of the cutting tool edge relative to the workpiece. When cutting metals, intense heat causes plastic deformation, producing chips or a curl of material.

Green ceramic is different; it is machined by a process of fracturing the material rather than a plastic deformation. The cutting edge *crushes* the ceramic just ahead of the tool edge as it moves through the material. This forms small particles, resulting in ceramic powder as an end product rather than chips or a curl, as when cutting metal. The ceramic cutting process does not generate high temperatures.

Attention must be paid to the avoidance of chipping at the edge of a workpiece and development of internal cracking caused by compressive stresses.

Material abrasion

When cutting green ceramic, most tool wear is caused by the abrasive nature of the ceramic particles rather than by material temperature or cutting speed. This places emphasis on selecting the most abrasion-resistant tool surface material, specifically, diamond.

Cutting speed

When cutting metals, the intense heat that is generated results in tool wear increasing rapidly with increase in cutting speed. The absence of elevated temperatures when machining green ceramic essentially eliminates speed as a contributor to tool wear.

Feed and depth of cut

Because small feeds and depths of cut do not lead to increasing the crushing effect on green ceramic, tool wear will advance rapidly with light feed, but stabilize as feed is increased. As the cutting action moves toward producing larger cracks and particles of removed material, flank wear of the cutting tool edge stabilizes. Therefore, in addition to increasing the volume of material removed, increasing feed can extend tool life.

The depth of cut should not exceed one-third of the tool diameter. Increasing the depth of cut to one-half the tool diameter will tend to break the material at the exit of a cut.

Determining tool life

Tool life is determined by the quality of the cutting edge and the thickness of the diamond layer at the cutting edge. Typically the tool will go through a break-in period that serves to refine the tool surface at the cutting edge, resulting in an improved surface finish. This will be followed by a long period of consistent performance, with a very gradual thinning of the diamond due to workpiece abrasion.

End-of-life occurs when the diamond finally wears through, revealing the tungsten carbide substrate, or when the diamond surface develops a discontinuity. In either case the tungsten carbide wears rapidly at the cutting edge and the tool quickly becomes dull, resulting in poor surface finish of the workpiece.

Care and handling of diamond tools

Use the same care practiced with carbide tools when meas-

uring or setting up. This care should include optical measurements when possible, and the avoidance of any contact of the tool's cutting edges with the hard surfaces of micrometer anvils, gauge blocks and any other inspection or setup equipment. Machine setup, including "touching off", must be accomplished with a soft material (plastic, paper, etc.) between the tool and the touch off plate.

When storing *sp*³ tools, place them in the original containers provided. This will prevent the tools from touching each other or other hard surfaces in the storage area, or from rolling off the bench, which could result in chipping of the cutting edges.

Controlling dust and chips

Both compressed air and vacuum are required. It is essential to continually remove ceramic residue from the point of machining, because build-up of ceramic dust exacerbates tool wear and increases tool pressure, leading to possible fracturing of the workpiece material. Use of compressed air (15 to 20 psi) with two nozzles is recommended. One nozzle should be directed at the tool to prevent dust packing, the other in the general vicinity to stir the dust to aid removal by the vacuum system.

The residue from machining green ceramic will range from small particles (0.001" – 0.005") to fine dust. A dust collection system employing high velocity air is commonly used. A minimum air velocity of 500 ft/min is needed to capture the dust at the machining location. After capturing the dust an even higher velocity of 2000 ft/min should be used to prevent dust from settling in the exhaust ducts. Screening should be used in advance of the dust filters to catch large particles which might damage the filter system.

Clamping, fixturing and supports

The primary precaution is to avoid excessive clamping pressure. While the composition of green ceramics can range from "fairly strong" to "very soft", all workpieces must be viewed and treated as easily crushable. Unlike metals (aluminums, coppers, etc.) which can take on permanent warpage and deformation, green ceramic will fracture, especially parts with thin walls, and rods with a high length/diameter ratio.

Vacuum chucks and fixtures are the preferred method of holding workpieces. Vacuum works well for normal forces; for lateral forces a mechanical stop is required. Mechanical stops and clamps should be cushioned using PVC electrical tape. Neoprene should not be used as a cushioning or gripping material because it is too soft, resulting in vibration of the workpiece.

For turning, "pot" chucks made of a compressible material such as Delrin or Nylatron work well. The workpiece is inserted in the chuck's recess, and the chuck is then held and compressed in a conventional 6-jaw mechanical chuck. The pressure of the jaws compresses the pot chuck so as to grip the ceramic workpiece. To prevent slippage, the green ceramic should be wrapped in emery cloth, with the abrasive surface on the outside and double-sided adhesive tape between the emery cloth and the workpiece.

Minimize clamping pressure, relying on vacuum retention and methods such as emery cloth to prevent slipping.

Endmilling, drilling and profiling green ceramic

Endmilling

Tool configuration: use square endmills with a small radius whenever possible. Diamond tools are more brittle than carbide and sharp corners may break upon entry into a cut at high feed rates. A radius of 0.010" to 0.015" will greatly strengthen the tool, providing extra durability.

For roughing at high feed rates 2-flute endmills should be used to minimize the possibility of tool breakage from flute packing. For general purpose and finish cutting use 4 flutes; the cost for a CVD diamond endmill is the same, regardless of flute count. Improved surface finish and longer life usually result from multiple flutes in finishing operations.

Chipping: to avoid chipping, several techniques can be employed. Milling a short distance at the exit side of the part before starting the cut is very effective in avoiding breakout, just as chamfering the end of a cylinder is for turning. Lowering feed rates will lessen chipping upon exit, but directly affects productivity. Tool rotation can be used to lessen exit edge chipping for flat surfaces by using "climbing" rotation, in which the workpiece is fed into the direction of tool rotation, rather than conventional milling.

Machining parameters: starting conditions for milling vary considerably for green ceramic, but generally 200 sfm and 0.002 inches per flute per revolution is a conservative starting point for 1/4" diameter and larger endmills. The table details recommended starting parameters.

Starting parameters for endmilling green ceramic				
Endmill dia. in. (mm)	Machine speed rpm	Cutting speed sfm (m/min)	Operation	Feed rate fpt (mm)
1/64	6,000 to 10,000	25 to 40 (8 to 12)	Finish	.0002-.0005 (.005-.013)
1/32 (1.0)	6,000 to 10,000	50 to 80 (15 to 25)	Finish	.0005-.001 (.013-.025)
1/16 (2.0)	6,000 to 10,000	100 to 160 (30 to 50)	General Finish	.001-.002 (.025-.050) .0005-.001 (.015-.025)
1/8 (3.0)	6,000 to 10,000	200 to 325 (60 to 100)	General Finish	.001-.002 (.025-.050) .0005-.001 (.015-.025)
3/16 (5.0)	4,000 to 10,000	200 to 500 (60 to 150)	General Finish	.001-.002 (.025-.050) .0005-.001 (.015-.025)
1/4 (6.0)	3,000 to 10,000	200 to 650 (60 to 200)	General Finish	.002-.004 (.050-.100) .001-.002 (.025-.050)
5/16 (8.0)	2,500 to 10,000	200 to 800 (60 to 245)	General Finish	.002-.004 (.050-.100) .001-.002 (.025-.050)
3/8 (10.0)	2,000 to 10,000	200 to 1000 (60 to 300)	General Finish	.003-.005 (.075-.130) .001-.003 (.025-.075)
1/2 (12.0)	1,500 to 10,000	200 to 1300 (60 to 400)	General Finish	.003-.005 (.075-.130) .001-.003 (.025-.075)

rpm – revolutions per minute

sfm – surface feet per minute; m/min – meters per minute.

fpt – feed per tooth (feed per cutting edge/flute) in inches or (mm).

Feed per revolution (fpr) = feed rate (fpt) x no. of teeth (flutes).

Feed per minute (fpm) = fpr x rpm.

Drilling

Dust removal: to reduce tool wear and material chipping, the machining dust *must* be removed from holes during drilling. This is best accomplished by "peck" drilling—drilling in steps no greater than one-fourth of the drill diameter. Use two air nozzles, one to clear the dust from the drill when it is withdrawn, the other to clear the hole.

Machining parameters: the table shows starting machining parameters for drilling green ceramic. These conditions will vary according to the grade of ceramic being machined and the set-up and dust removal practices.

Starting parameters for drilling green ceramic			
Drill diameter inches (mm)	Peck size inches (mm)	Cutting speed sfm (m/min)	Feed rate ipr (mm/rev)
1/32-3/16 (1.0-5.0)	1/128-3/64 (0.25-1.25)	200-1000 (60-300)	.001-.003 (.025-.075)
3/16-1/4 (5.0-6.0)	3/64-1/16 (1.25-1.5)		.002-.004 (.025-.100)
1/4-5/16 (6.0-8.0)	1/16-5/64 (1.5-2.0)		.002-.005 (.025-.130)
5/16-3/8 (8.0-10.0)	5/64-3/32 (2.0-2.5)		.002-.006 (.025-.150)
3/8-1/2 (10.0-12.0)	3/32-1/8 (2.5-3.0)		.002-.008 (.025-.200)

ipr – inches per revolution; mm/rev – millimeters per revolution

Profiling

The table shows parameters for Dapra-style ball nose, flat bottom and back draft profiling cutters. sp^3 profiling inserts are also available for Valenite Widia and Millstar tools.

Starting parameters for profiling green ceramic				
Cutting dia. inches (mm)	Machine speed rpm	Cutting speed sfm (m/min)	Operation	Feed rate fpt (mm)
5/16 (7.94)	7,500 to 16,000	640 to 1,320 (195 to 400)	General	.005 - .008 (.130 - .200)
			Finish	.001 - .004 (.025 - .100)
3/8 (9.53)	6,500 to 13,500		General	.005 - .008 (.130 - .200)
			Finish	.001 - .004 (.025 - .100)
1/2 (12.7)	4,900 to 10,000		General	.009 - .015 (.230 - .400)
			Finish	.002 - .008 (.050 - .200)
5/8 (15.9)	3,900 to 8,000		General	.009 - .015 (.230 - .400)
			Finish	.002 - .008 (.050 - .200)
3/4 (19.1)	3,200 to 6,700		General	.009 - .015 (.230 - .400)
			Finish	.002 - .008 (.050 - .200)
1 (25.4)	2,400 to 5,000	General	.013 - .020 (.330 - .500)	
		Finish	.004 - .012 (.100 - .300)	
1-1/4 (31.8)	2,000 to 4,000	General	.013 - .020 (.330 - .500)	
		Finish	.004 - .012 (.100 - .300)	

rpm – revolutions per minute.

sfm – surface feet per minute; m/min – meters per minute.

fpt – feed per tooth (feed per cutting edge/flute) in inches or (mm).

Turning and milling green ceramic with inserted cutters

General

Tool configuration: Disposable inserts with a $1/64$ " to $1/32$ " nose radius are most effectively used for turning and milling green ceramic. A positive rake insert with a ground flank is preferred.

Surface finish: finish can be improved by selecting the appropriate tool geometry and feed rates. Larger nose radii will improve finish, but with increased tool pressure. A smaller nose radius will relieve pressure, but feed must be reduced to achieve comparable surface

finish. DOC will not affect surface finish unless it causes excess tool pressure resulting in vibration, or if it is too light (under 0.005") to remove an adequate amount of material.

Breakout: breakout at the end of a pass is always a concern. This can be avoided by having a chamfer cut at the end of the part to ease exit of the tool, or provide stock which can later be cut off. Avoid square-nosed cut-off tools to prevent breaking prior to completion of the cut. A 20° relief angle is recommended.

Turning

Workpiece configuration: when machining long rods and cylinders, higher speeds and depths of cut can be employed with higher strength materials.

Depth-of-cut: DOC should always be maximized when possible without incurring distortion of the part. When distortion or "whip" are present, feed and DOC must be adjusted. Lower feed rates will allow holding deeper cuts. Feed rates of 0.005" per revolution for roughing and between 0.001" and 0.003" for finishing might be necessary. Deeper cuts always generate higher pressures and larger fracturing particles, thereby producing rougher surface finish.

Machining parameters: The following starting parameters are recommended for general purpose and finish turning.

Starting parameters for turning green ceramic		
Operation	Cutting speed sfm (m/min)	Feed rate ipr (mm/rev)
General purpose	100–500 (30–150)	.002–.010 (.050–.250)
Finish		

sfm – surface feet per minute; m/min – meters per minute.
ipr – inches per revolution; mm/rev – millimeters per revolution

Milling

Workpiece configuration: When milling large surfaces or volumes, higher speeds and depths of cut can be employed. Use higher strength materials when there are thin walls involved.

Depth-of-cut: DOC should always be maximized when possible, to reduce multiple passes. Lower feed rates will allow holding deeper cuts. Feed rates of 0.004"/tooth/revolution for roughing and between 0.0005" and 0.002"/tooth/revolution for finishing might be necessary.

Multiple cutters: for multiple-pocket milling cutters it is recommended that axial alignment be used to align all inserts within ± 0.0002 " for best results. This will improve surface finish and reduce insert wear, as all the inserts will be cutting equally.

Machining parameters: The following starting parameters are recommended for general purpose and finish milling.

Starting parameters for milling green ceramic		
Operation	Cutting speed sfm	Feed rate in/tooth (mm/tooth)
General purpose	500–1000 150–300)	.002–.006 (.050–.150)
Finish		

sfm – surface feet per minute; m/min – meters per minute.

Diamond tools available from sp^3

Endmills

Fractional inch size endmills are available from sp^3 in diameters from $1/64$ " to $1/2$ ". Over 150 styles include 2, 3 and 4 flutes, in standard and extended lengths. Metric endmills are available in diameters from 1.0 to 12.5 mm, in various lengths. End styles offered are square (with an end grind angle 1° to 3° concave) and ball end. Square-end endmills with a corner radius of .015" and .030" are available in several standard sizes. Optionally, any standard endmill may be ordered with a corner radius. sp^3 also offers **profiling endmills**.

For deep, zero draft machining of green ceramic, sp^3 offers **premium endmills** with a relieved shank allowing a typical reach of 10 diameters. The premium endmills are available in fractional inch diameters from $1/64$ " (0.16" reach) to $1/4$ " (2.5" reach), and metric diameters of 1.0, 2.0, and 3.0 mm. Standard end styles are square and ball nose; corner-radiused tools can be ordered.

Drills

sp^3 drills are industry-standard 2-flute spiral, with a 118° four-facet point. Drills are available in over 150 diameters in fractional inch, wire and letter sizes from #70 (0.0280") to $1/2$ ", and in metric sizes from 1.0 to 12.5 mm. sp^3 will supply custom drills in diameters from $1/32$ " to $1/2$ " (1 mm to 12.5 mm) and lengths to 6 inches (150 mm).

sp^3 also offers **spotting drills** and **center drills**.

Routers

If you are using diamond pattern routers for side cutting fiberglass, consider switching to sp^3 multi-flute routers. These routers will give significantly longer tool life coupled with higher feed rates. A 10° helix angle ensures that there will be minimal material deflection force on thin panels. Use our standard endmill table for machining guidelines and adjust spindle speeds and feeds for 8 flutes.

Inserts

sp^3 offers over 240 insert styles, including multiple cutting edges, chip breakers, and geometries not possible with PCD tooling in many cases. The corner-to-corner coating uniformity of sp^3 inserts allows indexing without machine readjustments.

Insert shapes available include diamond (35° , 55° and 80°), triangle, square and round. All inserts are ANSI standard sizes and tolerances. Sizes (inscribed circle) range from $1/4$ " to $1 1/4$ ". Styles include screw-down, pin-held and clamp.



sp^3 's offering of diamond tools encompasses over 500 styles of endmills, drills, insertable cutters, routers, saws, and other tools.

Profiling inserts

Styles available: profiling inserts are available in three styles: ball nose, flat bottom and backdraft.

Ball nose cutters are designed to ramp up or down, and center cut, allowing for blending complex contours, shapes, cores and cavities.

Flat bottom cutters are designed for draft walls with only the corner radius of the insert engaged in the cut. This style reduces cutting pressure and deflection.

Back draft cutters are designed for straight walls and long extension in milling hard to reach areas in cores and cavities.

sp^3 offers as standard products Dapra-style profiling inserts in sizes ranging from $5/16$ " to $1 1/4$ ". The standard corner radius is $1/16$ "; tools may be ordered with a radius of $1/32$ ". Millstar and Valenite Widia styles are available on special order.

Saws

sp^3 offers diamond saws for slotting and other applications in a broad range of materials. The saws come in four standard widths and a coarse tooth pitch suitable for nonmetallic materials. Machining parameters are basically the same as for carbide saws although significantly higher speeds can be used in some materials, such as green ceramic.

Custom coating

sp^3 will coat customer-supplied tungsten carbide tools, such as inserts, endmills, drills, and grooving inserts. These may be standard tools purchased by the customer or tools manufactured to a special configuration. sp^3 will also have tools ground to a customer-supplied print. Consult the sp^3 catalog or website for acceptable carbide grades for diamond coating.

Call 800-773-9940 for a complete sp^3 tool catalog, or visit our website www.sp3inc.com

About sp^3

Founded in 1993 and located in California's Silicon Valley, sp^3 specializes in the development and manufacture of diamond cutting tools.

These products encompass a wide range of cutting tools for abrasive non-metallic materials and non-ferrous metals, as well as seals and other wear parts. Polycrystalline diamond is grown on the surface of endmills, drills, inserts and other tools in a chemical vapor deposition or "CVD" reactor. The result is a pure diamond surface, with no metallic binder. sp^3 uses patented manufacturing processes and deposition systems designed and built by sp^3 .

The MAC system

sp^3 offers its DIAbide tools in different surface configurations to optimize performance with specific workpiece materials and machining operations. These configurations are identified by Material Application Codes, or "MACs." MACs are expressed as a 1- or 2-digit suffix to the part number, for example 12085-7 or TPG-432-18.

Higher numbered MACs represent a thicker diamond surface and a more robust tool; lower numbered MACs tend to have a sharper edge. For less abrasive and less brittle materials, a smoother finish may be obtained with a lower MAC. sp^3 recommends using the lowest MAC that is suitable for the material to be machined.

A complete guide to the MAC system is included in the sp^3 diamond tool catalog and on the sp^3 website.

sp^3 's website

- The website offers a wealth of information:
- A complete on-line catalog
- Guidance on selecting the optimum tool for your application via the Material Application Code
- New product information
- Information on custom coating services
- Information on CVD technology
- Machining parameters
- Descriptions of tool applications in various workpiece materials
- Comparative tool tests
- Current and archive copies of the newsletter *Spotlight on sp^3*
- Magazine articles featuring diamond tools
- Notice of tradeshow at which sp^3 will be exhibiting
- The ability to request literature, request sample tools, and order tools
- Company information, including employment

With the deposition process completely under computer control, the sp^3 Model 600 Reactor produces tools and other products with a uniform, consistent diamond surface, in high volume.



The reactor design allows large quantities of diamond tools and other diamond items to be produced per deposition cycle.



Evaluation sample tools

If you have an application that is unproven with diamond tools, sp^3 will provide samples for your evaluation.

We realize there is a cost on your part to test a new tool, just as there is a cost to sp^3 in supplying samples. However, without testing it is hard for both the tool supplier and the tool user to make advancements. We hope that your efforts will be rewarded with a success that reduces your overall costs or helps you solve a machining problem that hasn't had a satisfactory answer in the past.

Testing is also very important for sp^3 . Shared results from your testing help sp^3 to better understand how our tools performed in your application, allowing us to optimize our products to better meet your needs.

When we supply evaluation samples, we ask that you complete the brief Field Evaluation Report we supply with the samples and return it, along with the tested tools, when you have completed your evaluation. We learn a great deal about our tools' performance by inspecting them after they have been tested, and we can often recommend adjustments to your application or improve our process to provide your company with even greater productivity gains or tooling cost reductions.

To request an evaluation sample do one of the following:

- Call your sp^3 tool distributor
- Call sp^3 at 800-773-9940
- Use the sample request on our website, www.sp3inc.com

For assistance call: 800-773-9940
Visit our website: www.sp3inc.com